

# -SEE705

## **PSD Signal Processing System**

### Part number: SE-0018 Description: SEEPOS

The SiTek SEEPOS is a versatile PSD signal processing tool optimized for development of PSD systems. High speed PSD electronics combined with digital signal processing and high speed USB data transfer gives a powerful measurement system. With its large dynamic range it can handle light powers from nW to mW from DC light sources as well as modulated light sources.

All parameters, such as PSD bias voltage, amplifier gain, the use of analog and digital filters etc., are easily controlled from the included software and light spot position is continuously displayed both in XY and X-t, Y-t graphs. Optimized plot algorithms ensure that all data is visually seen on the screen even in full speed measurements. Included tools for data analysis and visualization simplify rapid scan through large data sets in order to find specific parts of interest.



### **Technical Specification**

#### **Parameters**

#### **Analog Part**

Input photo current range Pre amplifier gain PSD bias voltage HP-filter cutoff frequency

#### **Digital Part**

A/D conversion Sampling frequency Light source trigger frequency (TTL) Computer interface

#### Others

External light source trigger frequency (TTL) PSD interface Dimensions W x H x L 50 nA – 5 mA 1000 V/A, 50 000 V/A 0-30 V (continuously variable) 150 Hz (on/off)

16 bit 1MHz (parallel) DC - 250 kHz USB2.0

DC - 100 kHz DSUB9 124,4mm x 36,2mm x 148mm



PEO B.V.

info@gotopeo.com www.gotopeo.com The Netherlands Havenweg 16, 6603 AS Wijchen +31 (0)24 648 86 88

Belgium Watermolenstraat 2, B-2910 Essen +32 (0)3 309 32 09

CoC 34107894 VAT NL807859151B01 IBAN NL29 RABO 0356 1960 46 BIC RABONL2U



### Connection



### **Key Features**

- Extremely versatile all important parameters are easily adjusted
- Highest performance 16 bit A/D conversion at 1 MHz and full speed USB data transfer
- User friendly intuitive interface based on LabView
- Suitable for all users Easy set-up and advanced analyzing functions included

### **Example of Applications**

- Development measurements
- Beam alignment
- Optical system quality control
- Monitoring of vibration deflection and motion
- Target rotation and displacement
- Fast steering mirror measurement

### Setup



### Complete **SEEPOS** is delivered with: Hardware, Software, USB cable, Power supply and User manual.

Information in this data sheet is believed to be reliable. However, no responsibility is assumed for possible inaccuracies or omissions. Specifications are subjected to changes without notice.

SiTek Electro Optics AB, Ögärdesvägen 13A, S-433 30 Partille, Sweden Phone:+46 31 340 03 30, Fax: +46 31 340 03 40, Email: <u>info@sitek.se</u> Website: <u>www.sitek.se</u>



#### PEO B.V.

info@gotopeo.com www.gotopeo.com The Netherlands Havenweg 16, 6603 AS Wijchen +31 (0)24 648 86 88 Belgium Watermolenstraat 2, B-2910 Essen +32 (0)3 309 32 09

CoC 34107894 VAT NL807859151B01 IBAN NL29 RABO 0356 1960 46 BIC RABONL2U



PHOTONICS